

VAMP-TECH S.p.A Via delle Industrie 10/12 - 20874 Busnago (MB)

Phone +39.039.6957821 Fax: +39.039.6820563-6956388 E-mail: marketing@vamptech.it



HOSTAFORM® S 9363 | POM | Impact Modified

Description

Preliminary Data Sheet

Hostaform® acetal copolymer grade S 9363 is an impact modified grade for demanding applications. Hostaform® S 9363 provides good impact strength while improving modulus and weld line strength over standard impact modified grades such as Hostaform® S 9064.

Chemical abbreviation according to ISO 1043-1: POM-HI

Physical properties	Value	Unit	Test Standard
Density	1380	kg/m³	ISO 1183
Melt volume rate (MVR)	5.5	cm ³ /10min	ISO 1133
MVR test temperature	190	°C	ISO 1133
MVR test load	2.16	kg	ISO 1133
Mold shrinkage - parallel	1.8	%	ISO 294-4
Mold shrinkage - normal	1.6	%	ISO 294-4
Water absorption (23°C-sat)	0.8	%	ISO 62
Mechanical properties	Value	Unit	Test Standard
Tensile modulus (1mm/min)	2000	MPa	ISO 527-2/1A
Tensile stress at yield (50mm/min)	50	MPa	ISO 527-2/1A
Tensile strain at yield (50mm/min)	12	%	ISO 527-2/1A
Flexural modulus (23°C)	2000	MPa	ISO 178
Charpy impact strength @ 23°C	NB	kJ/m²	ISO 179/1eU
Charpy impact strength @ -30°C	NB	kJ/m²	ISO 179/1eU
Charpy notched impact strength @ 23°C	13.0	kJ/m²	ISO 179/1eA
Charpy notched impact strength @ -30°C	8.0	kJ/m²	ISO 179/1eA
Thermal properties	Value Value	Unit	Test Standard
Melting temperature (10°C/min)	166	°C	ISO 11357-1,-2,-3

Test specimen production	Value	Unit	Test Standard	
Processing conditions acc. ISO	9988-2		Internal	

84

148

1.1

1.1



ISO 75-1/-2

ISO 75-1/-2

ISO 11359-2

ISO 11359-2

DTUL @ 1.8 MPa

DTUL @ 0.45 MPa

Coeff.of linear therm. expansion (parallel)

Coeff.of linear therm. expansion (normal)

°C

°C

E-4/°C

E-4/°C




VAMP-TECH S.p.A Via delle Industrie 10/12 - 20874 Busnago (MB)

Phone +39.039.6957821 Fax: +39.039.6820563-6956388 E-mail: marketing@vamptech.it



HOSTAFORM® S 9363 | POM | Impact Modified

Typical injection moulding processing conditions



Pre Drying:

Drying is not normally required. If material has contacted moisture through improper storage and handling or through regrind use, dry to prevent splay and odor problems.

Drying time: 3 h

Drying temperature: 80 - 100 °C

Temperature:

	Mold	[®] Melt	[®] Nozzle	[®] Zone4	[®] Zone3	[®] Zone2	[®] Zone1	
min (°C)	60	180	180	180	180	180	170	
max (°C)	70	200	200	200	190	190	180	

Pressure:

, , coourc.				
	Inj press	Hold press	Back pressure	
min (bar)	600	600	0	
max (bar)	1200	1200	5	

Speed:

Injection speed: slow

Special Info:

Do not heat over 205 C (~400 F) to avoid burning and discoloring product.

Contact Information

Americas

Ticona North American Headquarters Product Information Service 8040 Dixie Highway Florence, KY 41042

USA

Tel.: +1-800-833-4882
Tel.: +1-859-372-3244
email: prodinfo@ticona.com
Ticona on the web: www.ticona.com

Europe

Ticona GmbH Information Service

Tel.: +49 (0) 180-5842662 (Germany) +49 (0) 69-30516299 (Europe)

Fax: +49 (0) 180-2021202 (Germany & Europe)

email: infoservice@ticona.de Internet: www.ticona.com



VAMP-TECH S.p.A Via delle Industrie 10/12 - 20874 Busnago (MB)

Phone +39.039.6957821 Fax: +39.039.6820563-6956388



HOSTAFORM® S 9363 | POM | Impact Modified

Customer Service Tel.: +1-800-526-4960 Tel.: +1-859-372-3214 Fax: +1-859-372-3125

General Disclaimer

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colorants or other additives may cause significant variations in data values

Properties of molded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use.

To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for

the accuracy and completeness of such information. The information contained in this publication should not be construed as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication.

Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To

Moreover, there is a need to reduce numan exposure to many materials to the lowest practical limits in view of possible adverse effects. To the the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any equipment, processing technique or material mentioned in this publication should satisfy themselves that they can meet all applicable safety and health standards. We strongly recommend that users seek and adhere to the manufacturer's current instructions for handling each material they use, and entrust the handling of such material to adequately trained personnel only. Please call the telephone numbers listed (+49 (0) 69 30516299 for Europe and +1 859-372-3244 for the Americas) for additional technical information. Call Customer Services for the appropriate Materials Safety Data Sheets (MSDS) before attempting to process our products.

The products mentioned herein are not intended for use in medical or dental implants.

© Copyright 2007, Ticona, all rights reserved. (Pub. 29-April-2013)

